

PCA-16-25MM2-2C



HELIAX® fiber adaptor, 2 Core DC Power Cable connection. Input Power Cable conductor size as 2.5mm²~25mm² and Output Power Cable conductor size as 2.5mm²~16mm². Shield contact size as 4~6mm². Glands at both ends providing a IP67 weatherproof performance.

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Power adapters
Product Brand	HELIAX®

General Specifications

Color	Black
-------	-------

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

Packaging and Weights

Packaging quantity	1
--------------------	---