

# A-100455

## Base Product



## Single Phase Meter Cabinet

- Sealed to outside environment
- Double wall construction

## Product Classification

### Product Type

Power supply enclosure

## General Specifications

### Access

Front door

### Accessories

Cable plate | In-ground root | Plinth

### Batteries Supported

0

### Batteries Supported, with optional battery pedestal

0

### Cabinet Type

Meter cabinet

### Color

Green | Green (RAL 6009) | Light Gray (RAL 7035) | Others available at additional cost

### Door Security

7 mm triangle lock

### Internal Mounting Surface

12 mm plywood backboard

## Dimensions

### Height

1016 mm | 40 in

### Width

660.4 mm | 26 in

### Depth

254 mm | 10 in

### Depth, without door

254 mm | 10 in

## Electrical Specifications

### ac Distribution Type

10-way metal enclosure

### ac Feeds, Outgoing, quantity

6

### Generator Connection

No connection

### Power Phase

Single

### Voltage

230 Vac

## Material Specifications

# A-100455

---

<b>Finish</b>	Powder coated
<b>Material Type</b>	Galvanized steel

## Packaging and Weights

<b>Weight, net</b>	35.834 kg   79 lb
--------------------	-------------------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system