

Micro Duct Cable Closure Kit for 12 (26)-way micro-duct cable and up to 6 (2) 1-way drops (12-way joints)

- Waterproof closure for micro duct cable connections in outside plant networks
- Fast and easy installation and re-entry process with the gel-sealing system
- No special tools or sealing replacement material required for installation and re-entry

OBSOLETE

This product was discontinued on: July 1, 2018

Product Classification

Regional Availability	Australia/New Zealand
Product Type	Micro duct cable closure
Product Series	MDCC


General Specifications

Cable Entry Drop Port Style	Round
Cable Entry Main Port Style	Round
Cable Ports, quantity	5
Cable Sealing Type	Compressed gel
Closure Sealing Type	Hinged with wedge
Closure Style	In-line
Color	Black
Mounting	Wall
Network Area Type	Distribution

Dimensions

Height	50 mm 1.969 in
Width	135 mm 5.315 in
Length	320 mm 12.598 in
Main Cable Diameter, maximum	35 mm 1.378 in

Dimension Drawing



Material Specifications

Material Type Rugged polymer

Environmental Specifications

Environmental Space Below ground | Buried

Qualification Standards IEC 61300, 1 m waterhead

Packaging and Weights

Packaging quantity 1

Packaging Type Box | Carton

Weight, net 0.8 kg | 1.764 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



