

# CZ8468-000 | FOWB-T-NNNNN



FOWB Fiber Optic Wall Box, empty for holding up to 12 adapters

## OBSOLETE

### Replaced By:

CZ3625-000  
BUDI-2S-T-00NNES

BUDI Fiber Optic Wall mount Enclosure, no adapters, single element FIST splice trays for SMOUV splices

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Product Type</b>	Fiber wall box
<b>Product Series</b>	FOWB

## General Specifications


<b>Adapters, quantity</b>	0
<b>Color</b>	Light gray
<b>Interface</b>	Unloaded
<b>Mounting</b>	Wall
<b>Splicing Capacity, maximum</b>	24

## Dimensions

<b>Height</b>	220 mm   8.661 in
<b>Width</b>	140 mm   5.512 in
<b>Depth</b>	35 mm   1.378 in

## Outline Drawing

# CZ8468-000 | FOWB-T-NNNNN



## Material Specifications

**Material Type** Thermoplastic

## Environmental Specifications

**Operating Temperature** -25 °C to +70 °C (-13 °F to +158 °F)

**Environmental Space** Indoor

**Flammability Rating** UL 94 V-0

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

