


2-2122145-4 | FMS-J-4-B-I-S5F-48-IN99-48-SP



FMS Fiber Optic Termination/Splice Panel, 2U, 19 in, 48 SC/UPC, multimode, OM3, black

Product Classification

| | |
|------------------------------|--------------------------|
| Regional Availability | India |
| Portfolio | CommScope® |
| Product Type | Fiber patch/splice panel |
| Product Series | FMS |

General Specifications

| | |
|--|------------------------------------|
| Functionality | Patching Splicing |
| Body Style | Symmetrical |
| Cable Exit Location | Rear, left side Rear, right side |
| Color | Black |
| Growth Configuration | Fully loaded |
| Interface, front | SC/UPC |
| Fiber Color Code | TIA-598 |
| Rack Type | EIA 19 in |
| Rack Units | 2 |
| Shelf Movement | Sliding |
| Splice Trays Included, quantity | 4 |
| Splicing Type | Heat shrink, single fiber fusion |
| Total Ports, quantity | 48 |

Dimensions

| | |
|---------------|--------------------|
| Height | 88.9 mm 3.5 in |
| Width | 482.6 mm 19 in |
| Depth | 320 mm 12.598 in |

Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Multimode

Fiber Type OM3

Insertion Loss, maximum 0.3 dB

Return Loss, minimum 45 dB

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|---|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

