



FMS Fiber Optic Termination Panel, 1U, 19 in, 24 LC/UPC, singlemode, OS2, black

Product Classification

| | |
|------------------------------|-------------------|
| Regional Availability | India |
| Portfolio | CommScope® |
| Product Type | Fiber patch panel |
| Product Series | FMS |

General Specifications

| | |
|------------------------------|-------------|
| Functionality | Patching |
| Body Style | Symmetrical |
| Color | Black |
| Color, front | Black |
| Interface, front | LC/UPC |
| Rack Type | EIA 19 in |
| Rack Units | 1 |
| Shelf Movement | Sliding |
| Total Ports, quantity | 24 |

Dimensions

| | |
|---------------|--------------------|
| Height | 44.45 mm 1.75 in |
| Width | 482.6 mm 19 in |
| Depth | 320 mm 12.598 in |

Material Specifications

| | |
|----------------------|---------------|
| Finish | Powder coated |
| Material Type | Steel |

Optical Specifications

| | |
|-------------------|------------|
| Fiber Mode | Singlemode |
|-------------------|------------|

| | |
|--------------------------------|--------|
| Fiber Type | OS2 |
| Insertion Loss, maximum | 0.3 dB |
| Return Loss, minimum | 20 dB |

Packaging and Weights

| | |
|---------------------------|-------------------|
| Included | Mounting hardware |
| Packaging quantity | 1 |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

