

# 760005595 | iP-600A-12-SC-MMF



iPatch® 600A Fixed Multimode Intelligent Fiber Panel, SC 12 port duplex

## OBSOLETE

This product was discontinued on: December 31, 2012

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch panel
<b>Product Brand</b>	iPatch®

## General Specifications

<b>Color</b>	Black
<b>Intelligence Type</b>	iPatch® enabled
<b>Interface, front</b>	SC
<b>Rack Units</b>	1
<b>Shelf Movement</b>	Fixed
<b>Total Ports, quantity</b>	12

## Dimensions

<b>Height</b>	44.45 mm   1.75 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	223.52 mm   8.8 in

## Material Specifications

<b>Material Type</b>	Acrylonitrile butadiene styrene (ABS)   Polycarbonate (PC)
----------------------	--

## Optical Specifications

<b>Fiber Mode</b>	Multimode
-------------------	-----------

## Environmental Specifications

<b>Operating Temperature</b>	-5 °C to +50 °C (+23 °F to +122 °F)
------------------------------	-------------------------------------

# 760005595 | iP-600A-12-SC-MMF

---

**Storage Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Relative Humidity** Up to 95%, non-condensing

**Flammability Rating** UL 94 V-0

**Safety Standard** ACMA | CE | CSA | UL

## Packaging and Weights

**Included** Cover | Four #12-24 mounting screws | Instruction sheet | One piece double sided tape | One set splice tray holders | Shelf | Two cable ties | Two wire retainers

**Packaging quantity** 1

**Weight, net** 1.814 kg | 4 lb

## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015

### Classification

Designed, manufactured and/or distributed under this quality management system

