



RJ45 Patch Panel, Q Series, category 6A, 24-port, black, ,UTP, loaded

OBSOLETE

This product was discontinued on: October 1, 2018

Product Classification

Regional Availability	Asia EMEA Latin America North America
Portfolio	NETCONNECT®
Product Type	RJ45 patch panel

General Specifications

ANSI/TIA Category	6A
Cable Type	Unshielded
Color	Black
Growth Configuration	Fully loaded
Interface, front	RJ45 jack
Panel Mounting	Flush
Panel Style	Straight
Rack Type	EIA 19 in
Rack Units	1
Termination Type	IDC
Total Ports, quantity	24
Transmission Standards	ANSI/TIA-568-C.2 ISO/IEC 11801 Class EA
Wiring	T568A T568B

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in

1-1671607-1

Material Specifications

Material Type High-impact, flame retardant, thermoplastic | Steel

Packaging and Weights

Packaging quantity 1

Packaging Type Bag | Box

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Included Products

- 1-1671660-2 – RJ45 Modular Jack Q-Series, category 6A, unshielded, 8-position