



PowerSUM 2500 Category 5 U/UTP Patch Panel, 24 port B wiring

## OBSOLETE

This product was discontinued on: February 28, 2017

### Replaced By:

760180000      Distribution Module Panel, Cat 5E, 1U, 24 port  
CPP-5E-DM-1U-24

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	SYSTIMAX®
<b>Product Type</b>	RJ45 patch panel
<b>Product Brand</b>	PowerSUM

## General Specifications

<b>ANSI/TIA Category</b>	5
<b>Cable Type</b>	Unshielded
<b>Color</b>	Black
<b>Intelligence Type</b>	Passive
<b>Panel Style</b>	Straight
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	1
<b>Total Ports, quantity</b>	24
<b>Wiring</b>	T568B

## Dimensions

<b>Height</b>	44.45 mm   1.75 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	40.64 mm   1.6 in

## Material Specifications

**Material Type** High-impact, flame retardant, thermoplastic | Powder-coated steel

## Environmental Specifications

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

**Storage Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Relative Humidity** Up to 95%, non-condensing

**Flammability Rating** UL 94 V-0

**Safety Standard** UL | cUL

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant
UK-ROHS	Compliant

