



PowerSUM 2500 Category 5 U/UTP Patch Panel, 48 port B wiring

OBSOLETE

This product was discontinued on: February 28, 2017

Replaced By:

760180018 Distribution Module Panel, Cat 5E, 2U, 48 port
CPP-5E-DM-2U-48

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	RJ45 patch panel
Product Brand	PowerSUM

General Specifications

ANSI/TIA Category	5
Cable Type	Unshielded
Color	Black
Intelligence Type	Passive
Panel Style	Straight
Rack Type	EIA 19 in
Rack Units	2
Total Ports, quantity	48
Wiring	T568B

Dimensions

Height	88.9 mm 3.5 in
Width	482.6 mm 19 in
Depth	40.64 mm 1.6 in

Material Specifications

Material Type High-impact, flame retardant, thermoplastic | Powder-coated steel

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Relative Humidity Up to 95%, non-condensing

Flammability Rating UL 94 V-0

Safety Standard UL | cUL

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

