

RJ45 Patch Panel, SL Series, Modular standard, category 6 , unshielded, loaded, 96-port

OBSOLETE

This product was discontinued on: October 1, 2018

Replaced By:

760237041 CPP-UDDM-SL-2U-48	Discrete Distribution Module Panel, SL, UTP, 2U, 48 port
9-1375055-2	SL110 Series Modular Jack, RJ45, category 6, T568A/T568B, unshielded, without dust cover, bag of 24, black

Product Classification

Regional Availability	Asia Latin America North America
Portfolio	NETCONNECT®
Product Type	RJ45 patch panel
Product Series	SL Series

General Specifications

ANSI/TIA Category	6
Cable Type	Unshielded
Color	Black
Growth Configuration	Fully loaded
Interface, front	RJ45 jack
Panel Mounting	Flush
Panel Style	Straight
Rack Type	EIA 19 in
Rack Units	4
Termination Type	IDC
Total Ports, quantity	96
Transmission Standards	ANSI/TIA-568-C.2 ISO/IEC 11801 Class E
Wiring	T568A T568B

Dimensions

Height	177.8 mm 7 in
---------------	-----------------

1375016-2

Width 482.6 mm | 19 in

Material Specifications

Material Type High-impact, flame retardant, thermoplastic | Steel

Packaging and Weights

Packaging quantity 1

Packaging Type Bag | Box

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

REACH-SVHC

ROHS

Classification

Below maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

