



LSA-PLUS® Comprotect Overvoltage Plug, 2/1, CP BOD180A1

OBSOLETE

This product was discontinued on: February 1, 2019

Replaced By:

CP-59091078-00
CP-5909 1 078-00

LSA-PLUS® Comprotect Overvoltage Plug, 2/1, CP OD180A1

Product Classification

Regional Availability	EMEA
Product Type	Overvoltage plug
Product Brand	LSA-PLUS®

General Specifications

Transmission Standards DIN EN 60068-2-1 | DIN EN 60068-2-2/3 | DIN EN 60068-2-6 | ITU-T K.12

Dimensions

Height	12.7 mm 0.5 in
Width	9.652 mm 0.38 in
Length	38.608 mm 1.52 in

Electrical Specifications

Capacitance	50 pF
Current Rating, maximum	0.06 A
dc Resistance, maximum	1 ohm
Dielectric Strength	1.8 kV
Safety Voltage Rating	180 V

59091078-00 | 59091078-00

Environmental Specifications

Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Storage Temperature	-40 °C to +80 °C (-40 °F to +176 °F)
Environmental Space	Indoor

Packaging and Weights

Packaging quantity	10
Packaging Type	Bag Box

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

