



GigaSPEED X10D® VisiPatch® 360 4U Patch Panel Kit (Kit includes 2 assemblies as shown)

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	Back mount frame kit
Product Brand	VisiPatch®

General Specifications

Product Design	VisiPatch® 360
ANSI/TIA Category	6A

Dimensions

Height	180.34 mm 7.1 in
Width	215.9 mm 8.5 in
Depth	287.02 mm 11.3 in

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	Austel CE UL cUL

Packaging and Weights

Included	Back panel Four label holders Four wiring block covers Four wiring blocks Thirty-two connecting blocks Twelve white labels
Packaging quantity	1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

760049445 | VP360-4U-32P

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

