

760105486 | MGS-CAP-GY-10



MGS Cap Kit with Strain Relief, Gray (MGS600 / MGS400 / MPS100 / UNJ10GT / UNJ600T) (10 ea/pkg)

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	Cap
Product Brand	GigaSPEED Xpress®

General Specifications

ANSI/TIA Category	5e 6 6A
Color	Gray

Material Specifications

Material Type	High-impact, flame retardant, thermoplastic
----------------------	---

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing
Flammability Rating	UL 94 V-0
Safety Standard	UL cUL

Packaging and Weights

Packaging quantity	10
---------------------------	----

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance

760105486 | MGS-CAP-GY-10

ROHS Compliant

UK-ROHS Compliant

