

# 760231464 | SD-4U



Standard Density 4U sliding Panel, accepts (12) LGX/1000 style splice cassettes, modules or panels, providing up to 144 duplex LC ports

## OBSOLETE

This product was discontinued on: October 31, 2022

### Replaced By:

760251049  
EPX-4U-PNL-ENC

EPX 4U sliding panel, accepts (12) LGX/PNL style splice cassettes, modules or panels, providing up to 144 duplex LC ports

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch panel
<b>Product Series</b>	SD

## General Specifications

<b>Application</b>	Accepts twelve LGX/1000 footprint panels/cassettes
<b>Color</b>	Black
<b>Interface, front</b>	Unloaded
<b>Rack Units</b>	4
<b>Shelf Movement</b>	Sliding
<b>Total Ports, quantity</b>	0

## Dimensions

<b>Height</b>	177.8 mm   7 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	485.14 mm   19.1 in

## Material Specifications

# 760231464 | SD-4U

---

**Material Type** Acrylonitrile butadiene styrene (ABS) | Polycarbonate (PC) | Steel

## Environmental Specifications

**Flammability Rating** UL 94 V-0

## Packaging and Weights

**Packaging quantity** 1

**Weight, net** 11.113 kg | 24.5 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

