



Unloaded Foldable UCP Patch Panel with Cable Management, 1U Angle, FTP, 24-port

- The panel has four preinstalled Quick-Fit copper housing modules
- The housing modules are pre-assembled with ID number labels
- The housing modules fit all SL Series modular jacks

OBSOLETE

This product was discontinued on: November 1, 2018

Replaced By:

760237050 CPPR-SDDM-SL-1U-24 Recessed Angled Discrete Distribution Module Panel, SL, STP, 1U, 24 port

Product Classification

Regional Availability	Asia Latin America North America
Portfolio	NETCONNECT®
Product Type	RJ45 patch panel

General Specifications

Application	For use with SL Series outlets
Color	Black
Growth Configuration	Unloaded
Interface, front	RJ45 jack
Panel Mounting	Flush
Panel Style	Angled
Rack Type	EIA 19 in
Rack Units	1
Termination Type	IDC
Total Ports, quantity	24

Dimensions

Height	44.45 mm 1.75 in
---------------	--------------------

1859843-1

Width 482.6 mm | 19 in
Depth 250 mm | 9.843 in

Material Specifications

Material Type High-impact, flame retardant, thermoplastic | Steel

Packaging and Weights

Included Cable management bar

Packaging quantity 1

Packaging Type Bag | Box

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

