

Vertical Power Distribution Strip, 125V, 15A, No Surge Protection with Circuit Breaker, Twistlock plug

OBSOLETE

This product was discontinued on: December 31, 2014

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Vertical power strip |
| Ordering Note | Not available in Mexico |

General Specifications

| | |
|-----------------------------|------------------------|
| Color | Black |
| On/Off Switch | No |
| Plug Standard | NEMA L5-15P, twistlock |
| Receptacle Standard | NEMA 5-15R |
| Receptacle, quantity | 20 |

Dimensions

| | |
|---------------------|--------------------|
| Height | 41 mm 1.614 in |
| Width | 1683 mm 66.26 in |
| Depth | 41 mm 1.614 in |
| Cable Length | 3 m 9.843 ft |

Electrical Specifications

| | |
|------------------------------|----------|
| Circuit Breaker | No |
| Current | 15 A |
| Power Frequency | 50/60 Hz |
| Power Rating, maximum | 1.4 kW |
| Surge Indicator | Yes |

760083634 | PSV5-15NP-CBTP

Surge Protection Yes
Voltage 125 V

Material Specifications

Finish Powder-coated, textured
Material Type Steel

Environmental Specifications

Safety Standard UL | cUL

Packaging and Weights

Included Instruction sheet | Plastic bottom mounting clip | Two #10-32 x 1/2 in panhead screws | Two plastic top mounting clips | Vertical PDU
Packaging quantity 1
Weight, net 5 kg | 11.023 lb

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

