



Vertical Power Distribution Strip, 125V, 15A, No Surge Protection, No Circuit Breaker, Twistlock plug

## OBSOLETE

This product was discontinued on: December 31, 2014

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Vertical power strip  |
| <b>Ordering Note</b>         | Not available in Mexico   |

## General Specifications

|                             |                        |
|-----------------------------|------------------------|
| <b>Color</b>                | Black                  |
| <b>On/Off Switch</b>        | No                     |
| <b>Plug Standard</b>        | NEMA L5-15P, twistlock |
| <b>Receptacle Standard</b>  | NEMA 5-15R             |
| <b>Receptacle, quantity</b> | 20                     |

## Dimensions

|                     |                    |
|---------------------|--------------------|
| <b>Height</b>       | 41 mm   1.614 in   |
| <b>Width</b>        | 1683 mm   66.26 in |
| <b>Depth</b>        | 28 mm   1.102 in   |
| <b>Cable Length</b> | 3 m   9.843 ft     |

## Electrical Specifications

|                        |      |
|------------------------|------|
| <b>Circuit Breaker</b> | No   |
| <b>Current</b>         | 15 A |

# 760083659 | PSV5-15NP-NBTP

---

|                              |          |
|------------------------------|----------|
| <b>Power Frequency</b>       | 50/60 Hz |
| <b>Power Rating, maximum</b> | 1.4 kW   |
| <b>Surge Indicator</b>       | No       |
| <b>Surge Protection</b>      | No       |
| <b>Voltage</b>               | 125 V    |

## Material Specifications

|                      |                         |
|----------------------|-------------------------|
| <b>Finish</b>        | Powder-coated, textured |
| <b>Material Type</b> | Steel                   |

## Environmental Specifications

|                        |          |
|------------------------|----------|
| <b>Safety Standard</b> | UL   cUL |
|------------------------|----------|

## Packaging and Weights

|                           |   |
|---------------------------|---|
| <b>Included</b>           | Instruction sheet   Plastic bottom mounting clip   Two #10-32 x 1/2 in panhead screws   Two plastic top mounting clips   Vertical PDU |
| <b>Packaging quantity</b> | 1   |
| <b>Weight, net</b>        | 5 kg   11.023 lb  |

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

