

760152371 | 360-iP-M-E-HD6B-1U-24



SYSTIMAX 360™ iPatch® Evolve High Density F/UTP Modular Panel, 24 port

OBSOLETE

This product was discontinued on: June 30, 2015

Replaced By:

760201178

360-iP-MFTP-E-HD6B-1U-24

SYSTIMAX 360™ iPatch® Evolve High Density F/UTP Modular Panel, 24 port

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio

SYSTIMAX®

Product Type

RJ45 patch panel

Product Brand

SYSTIMAX 360™ | iPatch®

General Specifications

ANSI/TIA Category

6 | 6A

Cable Type

Shielded

Color

Cool gray

Intelligence Type

iPatch® enabled

Panel Style

Straight

Rack Units

1

Total Ports, quantity

24

Wiring

T568A | T568B

Dimensions

Height

44.45 mm | 1.75 in

Width

482.6 mm | 19 in

Depth

38.1 mm | 1.5 in

Compatible Diameter Over Dielectric, maximum

1.168 mm | 0.046 in

760152371 | 360-iP-M-E-HD6B-1U-24

Compatible Diameter Over Dielectric, minimum 0.762 mm | 0.03 in

Electrical Specifications

Current Rating at Temperature 1.5 A @ 20 °C | 1.5 A @ 68 °F

Dielectric Withstand Voltage, RMS, conductive surface 1,500 Vac @ 60 Hz

Dielectric Withstand Voltage, RMS, contact-to-contact 1,000 Vac @ 60 Hz

Insulation Resistance, minimum 500 MOhm

Material Specifications

Material Type Acrylonitrile butadiene styrene (ABS) | Polycarbonate

Environmental Specifications

Operating Temperature -5 °C to +50 °C (+23 °F to +122 °F)

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Relative Humidity Up to 95%, non-condensing

Flammability Rating UL 94 V-0

Safety Standard ACMA | CE | UL | cUL

Packaging and Weights

Included Cable management bar | Four #12-24 dog point mounting screws | Instruction sheet | Modular jacks (24) | Panel | Two #12 washers | Two #12-24 screws

Packaging quantity 1

Weight, net 0.726 kg | 1.6 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

