

# 760206540 | 360DMis-24LC-SM



G2 LL Singlemode MPO 12 distribution module, 24 LC to 2x12f MPO's pinned, internal shutters

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Fiber module  |
| <b>Product Brand</b>         | InstaPATCH® 360   |
| <b>Product Series</b>        | G2  |

## General Specifications

|                                |                    |
|--------------------------------|--------------------|
| <b>Functionality</b>           | Breakout           |
| <b>Color, front</b>            | Blue               |
| <b>Color, rear</b>             | Gray               |
| <b>Interface, front</b>        | LC/UPC             |
| <b>Interface, rear</b>         | MPO                |
| <b>Interface Feature, rear</b> | Key up/up   Pinned |
| <b>Polarity</b>                | Method B           |
| <b>Shuttered</b>               | Yes                |
| <b>Total Fibers, quantity</b>  | 24                 |

## Dimensions

|               |                      |
|---------------|----------------------|
| <b>Height</b> | 25.51 mm   1.004 in  |
| <b>Width</b>  | 95.91 mm   3.776 in  |
| <b>Depth</b>  | 119.69 mm   4.712 in |

## Optical Specifications

|                                |            |
|--------------------------------|------------|
| <b>Fiber Mode</b>              | Singlemode |
| <b>Fiber Type</b>              | OS2        |
| <b>Insertion Loss, maximum</b> | 1.05 dB    |

## Environmental Specifications

**Qualification Standards** IEC 61753-1 | TIA-568.3-D

**Safety Standard** CE | CSA | UL

## Packaging and Weights

**Packaging quantity** 1

**Weight, net** 0.109 kg | 0.24 lb

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |

