



## 1100 ANGLED GS6 PANEL KIT - 2U

### Product Classification

#### Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

#### Portfolio

SYSTIMAX®

#### Product Type

RJ45 patch panel

### General Specifications

#### ANSI/TIA Category

6A

#### Cable Type

Unshielded

#### Color

Black

#### Modules, quantity

8

#### Panel Style

Angled

#### Rack Type

EIA 19 in

#### Rack Units

2

#### Total Ports, quantity

48

### Dimensions

#### Height

88.9 mm | 3.5 in

#### Width

482.6 mm | 19 in

#### Depth

210.82 mm | 8.3 in

### Electrical Specifications

#### Current Rating at Temperature

1.5 A @ 20 °C | 1.5 A @ 68 °F

#### Dielectric Withstand Voltage, RMS, conductive surface

1,500 Vac @ 60 Hz

#### Dielectric Withstand Voltage, RMS, contact-to-contact

1,000 Vac @ 60 Hz

### Material Specifications

#### Material Type

Powder-coated steel

# 760206979 | 1100A-U-GS6-KIT-2U

---

## Mechanical Specifications

**Plug Insertion Life, test plug** IEC 60603-7 compliant plug

## Environmental Specifications

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

**Storage Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Relative Humidity** Up to 95%, non-condensing

**Flammability Rating** UL 94 V-0

**Safety Standard** UL | cUL

## Packaging and Weights

**Packaging Material** Eco-friendly, single-use plastics-free

**Packaging quantity** 1

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

