

FD3-AE288J00U20P1



FDH 3000 Small Fiber Distribution In-Hub Splice Cabinet, 288F, SC/APC, 0 splitters, LT pigtails, heat-shrink fusion, 12F

Product Classification

| | |
|------------------------------|------------------------|
| Regional Availability | North America |
| Product Type | Fiber distribution hub |
| Product Series | FDH 3000 |

General Specifications

| | |
|--|-----------------------|
| Access | Front |
| Cable Type | Pigtails - Loose Tube |
| Color | Putty white |
| Distribution Cables, quantity | 0 |
| Distribution Ports, quantity | 288 |
| Fibers per Feeder Cable, quantity | 12 |
| Mounting | Pad |

Dimensions

| | |
|-----------------------|------------------|
| Cable Length | 30.48 m 100 ft |
| Enclosure Size | Small |

Material Specifications

| | |
|----------------------|---------------|
| Finish | Powder coated |
| Material Type | Aluminum |

Environmental Specifications

| | |
|----------------------------|--------------|
| Environmental Space | Above ground |
|----------------------------|--------------|

Packaging and Weights

| | |
|---------------------------|--------|
| Packaging quantity | 1 |
| Packaging Type | Pallet |

FD3-AE288J00U20P1

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Above maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted

