

# PPP1248-E3-NS-S

---

PRO PATCH® Programmable 2 x 48 Bantam Panel, EDAC 3-pin, normals strapped with mating connector kit

**OBSOLETE**

This product was discontinued on: December 31, 2018

## Product Classification

<b>Regional Availability</b>	EMEA   Latin America   North America
<b>Product Type</b>	Audio patch panel
<b>Product Brand</b>	PRO PATCH®
<b>Product Series</b>	ProPatch

## General Specifications

<b>Application</b>	For use with Bantam audio patch cords
<b>Growth Configuration</b>	Fully loaded
<b>Interface, front</b>	Bantam jack
<b>Interface, rear</b>	EDAC receptacle
<b>Mounting</b>	Rack, horizontally oriented
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	1
<b>Total Ports, quantity</b>	96
<b>Wiring</b>	Normals strapped

## Dimensions

<b>Height</b>	44.5 mm   1.752 in
<b>Width</b>	482.6 mm   19 in

## Material Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Steel

## Mechanical Specifications

<b>Plug Insertion Force, maximum</b>	31 N   6.969 lbf
--------------------------------------	------------------

# PPP1248-E3-NS-S

---

<b>Plug Insertion Life, minimum</b>	20000 times
<b>Plug Retention Force, minimum</b>	9 N   2.023 lbf

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +65 °C (-40 °F to +149 °F)
<b>Storage Temperature</b>	-55 °C to +85 °C (-67 °F to +185 °F)
<b>Relative Humidity</b>	Up to 95%, non-condensing
<b>Environmental Standard</b>	MIL-STD-202
<b>Flammability Rating</b>	UL 94 V-0

## Packaging and Weights

<b>Included</b>	Mating connector kit
-----------------	----------------------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

