



AGILE 1U sliding panel, accepts (4) G2 modules or adapter packs providing up to 48 duplex LC or 32 MPO ports

OBSOLETE

This product was discontinued on: November 30, 2023

Replaced By:

760254918	EPX 1U open sliding panel, accepts (4) G2 style splice cassettes, modules or adapter packs, providing up to 48 duplex LC ports
EPX-1U-MOD-OPEN	

Product Classification

Regional Availability	EMEA
Regional Availability Note	Discontinued in all other regions since June 30, 2022 and replaced by 760249998 EPX-1U-MOD-ENC in North America, Latin America and Asia Pacific
Portfolio	CommScope®
Product Type	Fiber patch panel
Product Brand	AGILE™
Product Series	AGILE

General Specifications

Application	Accepts four G2 modular cassettes
Color	Black
Intelligence Type	Not iPatch® ready
Interface, front	Unloaded
Rack Type	EIA 19 in
Rack Units	1
Shelf Movement	Sliding
Total Ports, quantity	0

Dimensions

Height	43.5 mm 1.713 in
Width	482 mm 18.976 in

760242453 | AGL-1U-SL

Depth 270.8 mm | 10.661 in

Material Specifications

Finish Powder coated

Material Type Steel

Environmental Specifications

Safety Standard UL

Packaging and Weights

Packaging quantity 1

Weight, net 1.579 kg | 3.48 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

