

# A64507-000 | OCM5-SP21G00S2-30DASIA



OCM5 Fiber Optic Splitter Module, Planar, two 1x16 Splitters, singlemode, SC/APC, symmetrical split ratio, 3.0 m pigtailed

**OBSOLETE**

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Splitter module
<b>Product Series</b>	OCM5

## General Specifications

<b>Device Type</b>	Standard VAM
<b>Functionality</b>	Splitting
<b>Technology Type</b>	Planar lightwave circuit (PLC)
<b>Access</b>	Front
<b>Application</b>	For use with FIST cabinets
<b>Circuits, quantity</b>	2
<b>Distribution Type</b>	1 x 16 splitter
<b>Interface, Input</b>	SC/APC
<b>Interface, Output</b>	SC/APC
<b>Split Ratio</b>	Symmetrical
<b>Splitter, quantity</b>	2

## Dimensions

<b>Height</b>	154 mm   6.063 in
<b>Width</b>	16 mm   0.63 in
<b>Depth</b>	142 mm   5.591 in
<b>Pigtail Length, Input</b>	3 m   9.843 ft
<b>Pigtail Length, Output</b>	3 m   9.843 ft

## Packaging and Weights

**Packaging quantity** 1  
**Packaging Type** Box | Carton

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

