

# CU6826-000 | OCM5-SP11Z00L2-50DASIA



OCM5 Fiber Optic Splitter Module, Planar, one 1x64 Splitter, singlemode, LC/APC, symmetrical split ratio, 5.0 m pigtailed

**OBSOLETE**

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Splitter module
<b>Product Series</b>	OCM5

## General Specifications

<b>Device Type</b>	Standard VAM
<b>Functionality</b>	Splitting
<b>Technology Type</b>	Planar lightwave circuit (PLC)
<b>Access</b>	Front
<b>Application</b>	For use with FIST cabinets
<b>Circuits, quantity</b>	1
<b>Distribution Type</b>	1 x 64 splitter
<b>Interface, Input</b>	LC/APC
<b>Interface, Output</b>	LC/APC
<b>Split Ratio</b>	Symmetrical
<b>Splitter, quantity</b>	1

## Dimensions

<b>Height</b>	154 mm   6.063 in
<b>Width</b>	16 mm   0.63 in
<b>Depth</b>	142 mm   5.591 in
<b>Pigtail Length, Input</b>	5 m   16.404 ft
<b>Pigtail Length, Output</b>	5 m   16.404 ft

## Packaging and Weights

<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Box   Carton

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

