

459373-000 | XAGA-FOSC-B1



XAGA™ FOSC™ B1 Fiber Optic Splice Closure, Heat Shrink Cable sealing, complete kit with one pre-installed 24-splice tray (SM6 modules)

OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

| | |
|------------------------------|-------------------------------|
| Regional Availability | Latin America North America |
| Product Type | In-line, round fiber closure |
| Product Brand | FOSC® XAGA® |
| Product Series | XAGA FOSC |

General Specifications

| | |
|---------------------------------------|---------------------|
| Cable Blocking Components | None |
| Cable Ports Quantity, total | 2 round ports |
| Cable Sealing Type | Heat shrink |
| Closure Sealing Type | Wraparound sleeve |
| Closure Style | In-line |
| Color | Black |
| Network Area Type | Distribution |
| Splice Tray Included, quantity | 1 |
| Splice Tray Type Included | 24-way, heat shrink |
| Splicing Type, Supported | Single fusion |

Dimensions

| | |
|-----------------|--------------------|
| Length | 1016 mm 40 in |
| Diameter | 170.18 mm 6.7 in |

459373-000 | XAGA-FOSC-B1

Main Cable Diameter, maximum 25 mm | 0.984 in

Material Specifications

Material Type Fiber-reinforced multi-layer sealing sleeve

Environmental Specifications

Environmental Space Below ground | Buried

Packaging and Weights

Packaging quantity 1

Packaging Type Box | Carton

Weight, net 1 kg | 2.205 lb

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

