

# 760032268 | MODG2-6SC-SM-PT-A



G2 Modular Cassette with 6 SC TeraSPEED® Singlemode Pigtails, Type A

## OBSOLETE

### Replaced By:

760109553 360G2 Singlemode Fiber Cassette 6 SC with pigtails A  
360G2 Cartridge 6-SC-SM-BL-PIGTAILS A

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	SYSTIMAX®
<b>Product Type</b>	Fiber cassette with pigtails
<b>Product Brand</b>	TeraSPEED®

## General Specifications

<b>Adapter Color</b>	Blue
<b>Interface, front</b>	SC/UPC
<b>Interface, rear</b>	Stranded pigtail
<b>Total Fibers, quantity</b>	6
<b>Total Ports, quantity, front</b>	6

## Dimensions

<b>Height</b>	30.48 mm   1.2 in
<b>Width</b>	91.44 mm   3.6 in
<b>Depth</b>	119.38 mm   4.7 in
<b>Pigtail Length</b>	1.5 m   4.921 ft

## Optical Specifications

<b>Fiber Type</b>	G.652.D and G.657.A1, TeraSPEED®   OS2
<b>Insertion Loss, typical</b>	0.4 dB
<b>Return Loss, minimum</b>	55 dB

## Environmental Specifications

**Safety Standard** UL

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

**Agency**

**Classification**

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

## Included Products

760049783 – TeraSPEED® SC Multiport Shuttered Adapter, Blue, Single Pack  
SFA-SC06-BL-SHUTTERED