



Unshielded Discrete Distribution Module Panel, Keystone, 2U, 48 port, Black

## Product Classification

### Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

### Portfolio

CommScope®

### Product Type

RJ45 patch panel

### Product Series

KJ Series

## General Specifications

### Application

For use with Keystone outlets

### Cable Type

Unshielded

### Color

Black

### Panel Style

Straight

### Rack Type

EIA 19 in

### Rack Units

2

### Total Ports, quantity

48

### Wiring

T568A | T568B

## Dimensions

### Height

88.9 mm | 3.5 in

### Width

482.6 mm | 19 in

### Depth, with cable management

119.38 mm | 4.7 in

## Electrical Specifications

### Current Rating at Temperature

1.5 A @ 20 °C | 1.5 A @ 68 °F

### Dielectric Withstand Voltage, RMS, conductive surface

1,500 Vac @ 60 Hz

### Dielectric Withstand Voltage, RMS, contact-to-contact

1,000 Vac @ 60 Hz

## Material Specifications

**Material Type**

High-impact, flame retardant, thermoplastic | Powder-coated steel

## Environmental Specifications

**Operating Temperature**

-10 °C to +60 °C (+14 °F to +140 °F)

**Storage Temperature**

-40 °C to +70 °C (-40 °F to +158 °F)

**Relative Humidity**

Up to 95%, non-condensing

**Flammability Rating**

UL 94 V-0

**Safety Standard**

RCM | UL | cUL

## Packaging and Weights

**Packaging Material**

Eco-friendly, single-use plastics-free | Eco-friendly, single-use plastics-free

**Packaging quantity**

1

## Regulatory Compliance/Certifications

**Agency****Classification**

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

RCM

Compliant to electrical safety & telecommunications requirements

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

