



MRJ21™ Ultra Slim Cable Assembly, MRJ21 to MRJ21, 180°-180° 1GbE, 24-pair, CMP, 10 m, gray

- Universal modular copper cabling platform for applications such as Gigabit Ethernet, VoIP and Power over Ethernet
- Increased I/O port density and cleaner cabling schemes compared to RJ45 connectors and cabling
- Robust die cast cable covers provide straight, or 45 deg left/right cable exit for ease of routing

OBSOLETE

This product was discontinued on: June 1, 2022

Product Classification

| | |
|------------------------------|-------------------------------|
| Regional Availability | Latin America North America |
| Portfolio | CommScope® |
| Product Type | Copper trunk cable assembly |
| Product Brand | MRJ21™ |
| Product Series | MRJ21 |

General Specifications

| | |
|---------------------------------------|--------------------|
| ANSI/TIA Category | 6 |
| Application | Ethernet, 1 GbE |
| Cable Type | U/UTP (unshielded) |
| Conductor Type | Solid |
| Construction Type | Stranded |
| Interface, Connector A | MRJ21 plug |
| Interface Feature, connector A | Backshell, 180° |
| Interface, Connector B | MRJ21 plug |
| Interface Feature, connector B | Backshell, 180° |
| Jacket Color | Gray |
| Pairs, quantity | 24 |
| Total Ports, quantity | 6 |

1-2111367-0 | TMRJ-1UURG-SS010M

Dimensions

| | |
|--|-------------------|
| Cord Length | 10 m 32.808 ft |
| Diameter Over Jacket | 9.15 mm 0.36 in |
| Compatible Conductor Gauge, solid | 27 AWG |

Electrical Specifications

| | |
|------------------------------|-------|
| Safety Voltage Rating | 150 V |
|------------------------------|-------|

Material Specifications

| | |
|---------------------------|-------------|
| Conductor Material | Bare copper |
|---------------------------|-------------|

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Operating Temperature | -10 °C to +60 °C (+14 °F to +140 °F) |
| Environmental Space | Riser |
| Flammability Rating | CM |
| Safety Standard | cUL |

Packaging and Weights

| | |
|---------------------------|---|
| Packaging quantity | 1 |
|---------------------------|---|

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|---|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

