

# 760161380 | 360-imV-CNTRLR

## SYSTIMAX 360™ imVision® Controller



### **OBSOLETE**

This product was discontinued on: January 31, 2019

#### Replaced By:

760237876  
imV-CNTRL-X

imVision Controller X

## Product Classification

### Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

### Portfolio

SYSTIMAX®

### Product Type

Controller unit

### Product Brand

iPatch® | imVision®

## General Specifications

### Color

Cool gray

## Dimensions

### Height

81.28 mm | 3.2 in

### Width

19 mm | 0.748 in

### Depth

211.33 mm | 8.32 in

## Electrical Specifications

### Input Voltage

100–240 Vac

### Output Current at Voltage, continuous

1.25 A @ 12 Vdc

### Power Frequency

50–60 Hz

## Material Specifications

# 760161380 | 360-imV-CNTRLR

**Material Type** Acrylonitrile butadiene styrene (ABS) | Polycarbonate | Steel

## Environmental Specifications

**Operating Temperature** 0 °C to +50 °C (+32 °F to +122 °F)  
**Storage Temperature** -40 °C to +70 °C (-40 °F to +158 °F)  
**Relative Humidity** Up to 95%, non-condensing  
**Flammability Rating** UL 94 V-0  
**Safety Standard** C-Tick | CE | GOST | KC | cUL

## Packaging and Weights

**Included** 16 in panel bus jumper | 7 ft patch cord | Forty-four position bus panel | Power supply, 1.25A @ 12 Vdc output, 100-240 Vac 50-60 Hz input  
**Packaging quantity** 1  
**Weight, net** 1.288 kg | 2.84 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

