

SD-003UV



Static Desiccator Dehydrator with UV Filter

- To meet our global customer's RoHS environmental needs, we have changed our desiccant to a cobalt-chloride free desiccant. The compliant desiccant is orange when dry and turns green when saturated

Product Classification

Product Type Dehydrator

General Specifications


Dehydrator Type Desiccant
Desiccant Capacity 283 liters (10 cu ft) at 80% RH, +20 °C
Mounting Pole
Port Count 1
Port Type 3/8 in PE tube x 1/8 NPT

Dimensions

Product Height 127 mm | 5 in
Product Width 50.8 mm | 2 in
Product Depth 50.8 mm | 2 in
Volume Capacity, maximum 0.028 m³ | 0.999 ft³
Volume Capacity, minimum 0 m³ | 0 ft³

SD-003UV

Outline Drawing–Front



SD-003UV Front View

Environmental Specifications

Operating Temperature -29 °C to +49 °C (-20 °F to +120 °F)

Packaging and Weights

Height, packed	86 mm 3.386 in
Width, packed	165.1 mm 6.5 in
Depth, packed	121.9 mm 4.799 in
Weight, gross	0.9 kg 1.984 lb
Weight, net	0.2 kg 0.441 lb

SD-003UV

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

