



LightCrimp Plus™ Fiber Optic Connector Termination Tool Kit, LC/SC, without microscope

OBSOLETE

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber tool kit
Product Brand	LightCrimp Plus™
Product Series	LightCrimp

General Specifications

Interface	LC SC
------------------	---------

Environmental Specifications

Environmental Space	Indoor
----------------------------	--------

Packaging and Weights

Included	Alcohol fiber wipes Ball and hex key Carrying case Fiber cleaver Instruction sheet Kevlar cutter LC+ LC/SC cable holder Miller dual-hole strip tool Pro-crimper, LC+ LC/SC /Splice Slitter tool, 2 mm and 3 mm Stripper, micro-strip W/.008BLA Wrench, open end ¼
Packaging quantity	1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

1754845-1



Included Products

760243578 – Fiber Optic Hand Held Precision Cleaver
Tool



Fiber Optic Hand Held Precision Cleaver Tool

- Provides operator-independent precision quality cleaves in a hand held size
- Includes a blade knife with a 48,000 cleave lifetime
- Suited for field installable mechanical splice connectors, bare fiber adapters and fusion and mechanical splicing
- Supplied with a padded belt case with neck lanyard for convenience and storage

Product Classification

Regional Availability	Asia EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber tool kit

Dimensions

Height	46 mm 1.811 in
Width	53 mm 2.087 in
Length	55 mm 2.165 in

Environmental Specifications

Environmental Space	Indoor
----------------------------	--------

Packaging and Weights

Packaging quantity	1
Weight, net	500 g 1.102 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

