

Fiber Breakout Kit, outside plant cable

OBSOLETE

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	Fiber breakout kit, rectangular
Ordering Note	Order B sealant separately

General Specifications

Application	Buffers approximately 100 fibers
Color	Black
Compatible Interface	LC LC, keyed SC ST

Dimensions

Tube Inner Diameter	500 µm
Tube Outer Diameter	900 µm

Material Specifications

Material Type, body	Acrylonitrile butadiene styrene (ABS)
Material Type, tubing	PVC

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
------------------------------	--------------------------------------

Packaging and Weights

Included	Buffer tubing, 900 micron, 210 ft Clear PVC tubing, 1 ft, 0.234 in ID Clear PVC tubing, 2 ft, 0.166 in ID Clear PVC tubing, 25 ft, 0.095 in ID Eight unit splitter with clear cover Five syringes with applicator tip Heat shrink tubing, 2 ft, 0.187 in ID Instruction sheet Rosin bag Six clear PVC tubes, 2 in, 0.294 in ID Six unit splitter with clear cover Wire marker book
Packaging quantity	1

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

**Classification**

Designed, manufactured and/or distributed under this quality management system