

Wall Mount Building Entrance, top/bottom entry, up to 1728 splicing

**OBSOLETE**

**Replaced By:**

760183681  
WBE-FXS-EMT/18T

Wall Mount Building Entrance, universal entry, up to 864 single fusion splices

## Product Classification

<b>Regional Availability</b>	North America
<b>Portfolio</b>	Uniprise®
<b>Product Type</b>	Fiber wall box
<b>Product Series</b>	WBE

## General Specifications

<b>Application</b>	Accepts up to thirty-six mass, single, or mechanical fusion splice trays
<b>Cable Entry Location</b>	Bottom   Top
<b>Cable Entry, quantity, maximum, bottom</b>	6
<b>Cable Entry, quantity, maximum, left</b>	0
<b>Cable Entry, quantity, maximum, right</b>	0
<b>Cable Entry, quantity, maximum, top</b>	6
<b>Color</b>	Gray
<b>Interface</b>	Splicing only
<b>Mounting</b>	Wall

## Dimensions

<b>Height</b>	1,066.8 mm   42 in
<b>Width</b>	762 mm   30 in
<b>Depth</b>	318.77 mm   12.55 in

## Material Specifications

<b>Material Type</b>	Steel
----------------------	-------

Environmental Specifications

**Environmental Space** Indoor

Packaging and Weights

**Weight, net** 78.02 kg | 172.004 lb

Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

