

Wall Mount Building Entrance, side entry, up to 864 splicing

OBSOLETE

Replaced By:

760183681
WBE-FXS-EMT/18T

Wall Mount Building Entrance, universal entry, up to 864 single fusion splices

Product Classification

Regional Availability	North America
Portfolio	Uniprise®
Product Type	Fiber wall box
Product Series	WBE

General Specifications

Application	Accepts up to eighteen mass, single, or mechanical fusion splice trays
Cable Entry Location	Side
Cable Entry, quantity, maximum, bottom	0
Cable Entry, quantity, maximum, left	12
Cable Entry, quantity, maximum, right	12
Cable Entry, quantity, maximum, top	0
Color	Gray
Interface	Splicing only
Mounting	Wall

Dimensions

Height	622.3 mm 24.5 in
Width	762 mm 30 in
Depth	318.77 mm 12.55 in

Material Specifications

Material Type	Steel
----------------------	-------

Environmental Specifications

Environmental Space Indoor

Packaging and Weights

Weight, net 48.08 kg | 105.998 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

