

OCC1A Wideband Splitter, singlemode, 1x2, 55/45 ratio, 0.250 mm cable, light duty housing



Product Classification

| | |
|------------------------------|--------------------|
| Regional Availability | North America |
| Product Type | Splitter component |
| Product Series | OCC1A |

General Specifications

| | |
|---------------------------|--------------------------|
| Device Type | Component, tubular |
| Functionality | Splitting |
| Technology Type | Fused biconic tapered |
| Application | For use in FOSS closures |
| Circuits, quantity | 1 |
| Distribution Type | 1 x 2 splitter |
| Interface, Input | Stub tail |
| Interface, Output | Stub tail |
| Split Ratio | 55/45 |
| Splitter, quantity | 1 |

Dimensions

| | |
|---------------------------------|-------------------|
| Pigtail Length, Input | 2.5 m 8.202 ft |
| Pigtail Length, Output | 2.5 m 8.202 ft |
| Pigtail Diameter, Input | 0.25 mm 0.01 in |
| Pigtail Diameter, Output | 0.25 mm 0.01 in |

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

