



N-Type Female High Power Termination Load, 70–2700 MHz

OBSOLETE

This product was discontinued on: **March 31, 2012**

Replaced By:

7651928-00	N-Type Female High Power Termination Load, 70–3000 MHz
7651928-01	N-Type Female High Power Termination Load, 70–3000 MHz

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Termination Load

General Specifications

Device Type	Termination Load
Color	Silver
Interface	N Female

Electrical Specifications

Return Loss, minimum	20 dB
Average Power, maximum	200 W
Impedance	50 ohm
Operating Frequency Band	70 – 2700 MHz
Peak Power, maximum	1.5 kW
VSWR	1.25

Environmental Specifications

7116905

Operating Temperature	-33 °C to +85 °C (-27.4 °F to +185 °F)
Relative Humidity	46%–94%
Ingress Protection Test Method	IEC 60529:2001, IP30

Packaging and Weights

Height, packed	242 mm 9.528 in
Width, packed	165 mm 6.496 in
Length, packed	130 mm 5.118 in
Weight, gross	0.37 kg 0.816 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015



Classification

Designed, manufactured and/or distributed under this quality management system