



7-16 DIN Female High Power Termination Load, 70–2700 MHz

OBSOLETE

This product was discontinued on: **March 31, 2012**

Replaced By:

7651924-00	7-16 DIN Female High Power Termination Load, 70–2700 MHz
7651924-01	7-16 DIN Female High Power Termination Load, 70–2700 MHz

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Termination Load

General Specifications

Device Type	Termination Load
Color	Silver
Interface	7-16 DIN Female

Electrical Specifications

Return Loss, minimum	20 dB
Average Power, maximum	200 W
Impedance	50 ohm
Operating Frequency Band	70 – 2700 MHz
VSWR	1.25

Environmental Specifications

Operating Temperature	-33 °C to +85 °C (-27.4 °F to +185 °F)
------------------------------	--

7546395-00

Ingress Protection Test Method IEC 60529:2001, IP30

Packaging and Weights

Height, packed 242 mm | 9.528 in

Width, packed 165 mm | 6.496 in

Length, packed 130 mm | 5.118 in

Weight, gross 0.37 kg | 0.816 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015



Classification

Designed, manufactured and/or distributed under this quality management system