


FGS-KTW2-RL



FiberGuide® Vertical Duct Kit with 2in Slot Spacing and Hinged Cover, 6.58ft Length, 2x4in, Yellow

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Slotted vertical with hinged cover
Product Brand	FiberGuide®
Product Series	FGS

General Specifications

Product Feature	Slotted
Color	Yellow
Orientation	Vertical
Section Type	Straight section

Dimensions

Height	101.6 mm 4 in
Width	50.8 mm 2 in
Length	2,006.6 mm 79 in
System Dimensions	51 mm x 102 mm (2 in x 4 in)

Material Specifications

Material Type	Engineering Thermoplastic
----------------------	---------------------------

Environmental Specifications

Flammability Rating	CSA S143 UL 2024 UL 94 V-0
Halogen Characteristics	Blue Angel TCO '99 WEEE
Safety Standard	CSA UL

Packaging and Weights

FGS-KTW2-RL

Weight, net 3.164 kg | 6.975 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

