

# BHD-158

---



Double Block Hanger for 1-5/8 in coaxial cable - Hardware Sold Separately (search 243095-SERIES-HARDWARE for options available)

## Product Classification

<b>Product Type</b>	Hanger kit
<b>Product Brand</b>	HELIAX®
<b>Ordering Note</b>	ANDREW® standard product (Global)

## General Specifications

<b>Cables per Hanger</b>	2
<b>Color</b>	Black
<b>Hanger Type</b>	Double block hanger
<b>Mounting</b>	3/8 in (M10) drilled cable ladder

## Dimensions

<b>Maximum Stack Height</b>	4
<b>Height</b>	48 mm   1.89 in
<b>Width</b>	71.1 mm   2.799 in
<b>Length</b>	136.9 mm   5.39 in
<b>Compatible Cable Diameter Range</b>	49–51.1 mm
<b>Compatible Diameter, maximum</b>	51.1 mm   2.012 in
<b>Compatible Diameter, minimum</b>	49 mm   1.929 in
<b>Nominal Size</b>	1-5/8 in

## Electrical Specifications

<b>Return Loss Effect, maximum</b>	0.1 dB
<b>DTF Effect, maximum</b>	0.1 dB

## Material Specifications

# BHD-158

---

**Material Type** Engineered plastic

## Environmental Specifications

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

**Environmental Strength Capability** Double cable weight

**UV Resistance, minimum with no degradation** ≥100 hours exposure in accelerated UV life chamber

## Packaging and Weights

**Height, packed** 5.1 cm | 2.008 in

**Width, packed** 25.4 cm | 10 in

**Length, packed** 30.5 cm | 12.008 in

**Packaging quantity** 10

**Weight, gross** 1.38 kg | 3.042 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.andrew.com/ProductCompliance">www.andrew.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power