


CGT78

Connector Grounding Kit for Mounting Rail for 7/8 in connectors



OBSOLETE

This product was discontinued on: September 30, 2012

Product Classification

Product Type	Grounding kit
Ordering Note	CommScope® non-standard product

General Specifications

Cable Type	Corrugated
Grounding Kit Type	Connector Grounding Kits
Thread Size	3/8 in M10

Dimensions

Nominal Size	7/8 in
---------------------	--------

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Storage Temperature	-40 °C to +80 °C (-40 °F to +176 °F)

Packaging and Weights

Height, packed	152.4 mm 6 in
Width, packed	203.2 mm 8 in
Length, packed	25.4 mm 1 in
Included	3/8 in hardware One 3/8 channel nut with spring One aluminum channel

CGT78

Packaging quantity 1
Weight, gross 0.23 kg | 0.507 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant
UK-ROHS	Compliant

