

CV5889-000 | TENIO-B6-TRAY-S12



TENIO™ Splice Tray for small closures (B6 size) for up to 12 heat shrink splice protectors (SMOUV 45 mm)

- Fiber and cable technology independent
- Compatible with G652.D optical fiber

Product Classification

Regional Availability	Australia/New Zealand EMEA Latin America
Product Type	Fiber splice tray
Product Series	TENIO

General Specifications

Color	Gray
Splice Tray Chip Type	Heat shrink
Splice Tray Included, quantity	1
Splices per Tray, quantity	12

Dimensions

Splice Protector Length, maximum	47 mm 1.85 in
Splice Protector Length, minimum	44 mm 1.732 in
Splice Protector Diameter, maximum	2.6 mm 0.102 in
Splice Protector Diameter, minimum	2.2 mm 0.087 in

Material Specifications

Material Type	PBT PET
----------------------	-----------

Mechanical Specifications

Minimum Bend Radius, standard	30 mm 1.181 in
--------------------------------------	------------------

Environmental Specifications

Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
----------------------------	--------------------------------------

CV5889-000 | TENIO-B6-TRAY-S12

Environmental Space Outdoor

Packaging and Weights

Packaging quantity 12

Packaging Type Bag | Carton

Weight, net 0.1 kg | 0.22 lb

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

