

L6CLICK



Double Click-on Hanger for 1-1/4 in coaxial cable - Hardware Sold Separately (search 243095-SERIES-HARDWARE for options available)

Product Classification

Product Type	Hanger kit
Product Brand	HELIAX®
Ordering Note	ANDREW® non-standard product

General Specifications

Cables per Hanger	2
Color	Black
Hanger Type	Click-on hanger
Mounting	3/8 in (M10) drilled cable ladder

Dimensions

Maximum Stack Height	4
Height	51.1 mm 2.012 in
Width	70.1 mm 2.76 in
Length	133.1 mm 5.24 in
Compatible Cable Diameter Range	38.1–40.1 mm
Compatible Diameter, maximum	40.1 mm 1.579 in
Compatible Diameter, minimum	38.1 mm 1.5 in
Nominal Size	1-1/4 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

L6CLICK

Material Type Engineered plastic

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Environmental Strength Capability Double cable weight

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed 37.7 cm | 14.843 in

Width, packed 13.9 cm | 5.472 in

Length, packed 15 cm | 5.906 in

Packaging quantity 10

Weight, gross 1.34 kg | 2.954 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power