MC-SA12-B



Stand-off Arm with U-bolts, 12 in

Product Classification

Product Type Support arms for ring mount

General Specifications

Mounting Ring mount

Pipe, quantity 0

Dimensions

 Height
 254 mm | 10 in


 Width
 254 mm | 10 in


 Length
 304.8 mm | 12 in

 Stand-off Distance
 304.8 mm | 12 in

Outline Drawing







Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact your local ANDREW representative

Wind Rating Criteria One 72 in x 8 in panel antenna per sector

Wind Rating Test Method TIA/EIA-222-G

Packaging and Weights

Included Hardware | Stand-off arms | U-bolts

Packaging quantity 1

Weight, net 34.24 kg | 75.486 lb

Regulatory Compliance/Certifications

Agency Classification



MC-SA12-B

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

