

Outdoor Fiber Cable, 216-fiber, singlemode OS2, loose tube, blue

Product Classification

Regional Availability	Australia/New Zealand
Portfolio	CommScope®
Product Type	Fiber OSP cable
Product Series	O-LD


General Specifications

Cable Type	Loose tube
Subunit Type	Gel-filled
Jacket Color	Blue
Jacket Marking	Meters
Fibers per Subunit, quantity	6
Total Fiber Count	216

Dimensions

Diameter Over Jacket	8.9 mm 0.35 in
-----------------------------	------------------

Representative Image



Material Specifications

Jacket Material Nylon

Mechanical Specifications

Flex 25 cycles

Optical Specifications

Fiber Type OS2

Optical Specifications, Wavelength Specific

Standards Compliance TIA-492CAAB (OS2)

Environmental Specifications

Operating Temperature -10 °C to +70 °C (+14 °F to +158 °F)

Environmental Space Buried

Regulatory Compliance/Certifications

Agency	Classification
RCM	Compliant to electrical safety & telecommunications requirements



* Footnotes

64624447-216 | O-216-LD-8M-M12BL/20G/PE/PA

Operating Temperature Specification applicable to non-terminated bulk fiber cable