



Outdoor Fiber Cable, 48-fiber, singlemode OS2, loose tube, blue

## Product Classification

<b>Regional Availability</b>	Australia/New Zealand
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber OSP cable
<b>Product Series</b>	O-LD

## General Specifications

<b>Cable Type</b>	Loose tube
<b>Subunit Type</b>	Gel-filled
<b>Jacket Color</b>	Blue
<b>Jacket Marking</b>	Meters
<b>Fibers per Subunit, quantity</b>	6
<b>Total Fiber Count</b>	48

## Dimensions

<b>Diameter Over Jacket</b>	8.9 mm   0.35 in
-----------------------------	------------------

## Material Specifications

<b>Jacket Material</b>	Nylon
------------------------	-------

## Mechanical Specifications

<b>Flex</b>	25 cycles
-------------	-----------

## Optical Specifications

<b>Fiber Type</b>	G.652.D   OS2
-------------------	---------------

## Optical Specifications, Wavelength Specific

<b>Standards Compliance</b>	TIA-492CAAB (OS2)
-----------------------------	-------------------

## Environmental Specifications

**Operating Temperature** -10 °C to +70 °C (+14 °F to +158 °F)

**Environmental Space** Buried

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable