7-556212-2

AMPINNERGY® Power-to-Power Cable Assembly, 5-wire/3-circuit (3-1-1), shared neutral, 30 feet

- Used to jumper system components together
- Mates with line connector cable assemblies, power junction boxes, power distribution modules, zone distribution modules, and power transition units

OBSOLETE

This product was discontinued on: June 30, 2020

Product Classification

Regional Availability	North America
Product Type	Power-to-power cable assembly
Product Brand	AMPINNERGY®
Product Series	AMPINNERGY

General Specifications

Application	Power to power connection
Construction Type	Corrugated hose
Interface, Connector A	Power male plug
Interface, Connector B	Power male plug
Neutral Type	Shared
Wiring	5-Wire/3 Circuit (3-1-1)

Dimensions

Cord Length	9.14 m | 29.987 ft
Neutral Conductor Gauge, solid	10 AWG

Electrical Specifications

Current Rating, maximum	20 A
Voltage Rating, maximum	125 Vac | 250 Vac

©2020 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: September 19, 2020

7-556212-2

Environmental Specifications

Environmental Space	Indoor
Safety Standard	CEC 2015 | CSA 22.2 | NEC 2013 | UL 1286 | UL 183 | UL 498

Packaging and Weights

Packaging quantity	1
Packaging Type	Bag

©2020 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: September 19, 2020