MC-DPM35-84

GroundSmart® Monopole Co-location Dual Pipe Mount Kit, 4 ft 9 in face, includes pipe

Product Classification

Product Type	Co-location dual pipe mount kit

General Specifications

Pipe, quantity	2
Sectors, quantity	1

Dimensions

Height	2,133.6 mm | 84 in
Face Width	1.463 m | 4.8 ft
Width	1,447.8 mm | 57 in
Length	355.6 mm | 14 in
Pipe Length	2,133.6 mm | 84 in
Pipe Outer Diameter	88.9 mm | 3.5 in
Stand-off Distance	355.6 mm | 14 in

Material Specifications

Material Type	Hot dip galvanized steel

Mechanical Specifications

Wind Rating	120 mph (BWS) at 150 ft AGL | 140 mph (3-second gust) at 150 ft AGL using Exposure D per FBC
Wind Rating Criteria	Four 72 in x 8 in panel antennas per sector
Wind Rating Test Method	TIA/EIA-222-G

Packaging and Weights

Included	Dual pipe frames | Pipe mounts
Packaging quantity	1
Weight, net	92.896 kg | 204.8 lb

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 26, 2024

MC-DPM35-84

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

* Footnotes

Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 26, 2024