RF-NL7-3-96

Non-Penetrating Roof Frame, 7 ft face, three 3-1/2 in OD x 96 in pipes

Product Classification

Product Type	Non-penetrating roof frame

General Specifications

Mounting	Non-penetrating
Note	Four 96 in x 18 in panel antennas per sector
Pipe, quantity	3

Dimensions

Height	2,438.4 mm | 96 in
Face Width	2.134 m | 7 ft
Width	2,133.6 mm | 84 in
Length	2.53 m | 8.3 ft
Pipe Length	2,438.4 mm | 96 in
Pipe Outer Diameter	88.9 mm | 3.5 in

Material Specifications

Material Type	Hot dip galvanized steel

Mechanical Specifications

Wind Rating	For Specifications, please contact steelproducts@commscope.com or call 800-255-1479
Wind Rating Test Method	TIA/EIA-222

Packaging and Weights

Included	Rubber mats, with or without pipe mounts

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 2, 2024

RF-NL7-3-96

Packaging quantity	1
Weight, net	299 kg | 659.181 lb

* Footnotes

Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 2, 2024